


时间(DATE)	修正版本 (REV)	变更内容(CHANGES)
/	V1.0	/
/	/	/





SECTION A-A



Wires for Hall AWG30									
VCC	GND	На	Hb	Нс	L1	L2			
RED	BLK	BLU	GRN	YEL	/	/			
热敏型号: MF51B103F3950									

保密说明: PROPRIETARY AND CONFIDENTIAL

此份图纸包含的所有信息均只属于T-MOTOR财产。未经T-MOTOR书面许可,禁止部分或全部复制。 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF T-MOTOR. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF T-MOTOR IS PROHIBITED.



	签 名(NAME)	日期(DATE)	标题(TITLE)	无框内转电机			
制 图(DRAWN)	***	***	型号 (DWG. NO)	RI75-PH			
审核(CHECKED)	***	***	版本(REV)	V1.0	单位(UNIT)	mm	
此图纸标注的尺寸有限。个别尺寸公差据要求提供。 THIS IS A LIMITED DIMENSION DRAWING. SPECIFIC TOLERANCE AVAILABLE UPON REQUEST.			比例(SCALE)	1:1	视角(VIEW)		